

ULTRASONIC LABEL SENSORS UGUTI

WITH IO-LINK

iii di-soric

ULTRASONIC LABEL SENSORS WITH IO-LINK: UGUTI.

FLEXIBLE, FAST, PRECISE, SIMPLE AND RUGGED.

Ultrasonic label sensors do not just detect very thin and transparent foil labels. They also reliably detect metalized labels and provide sufficient clearance for thicker, folded booklets. The innovative dual operation concept—optionally implemented using IO-Link with the configuration and diagnostics of all sensor functions or using teach-in with manual threshold value adjustment using the **+-** buttons—makes it possible to put the sensor into operation quickly.

Rugged, compact design with straight or angled plug connector

di-soric

70 G6-B5 CE

in a metal housing with full encapsulation and IP67, compatible with standard mounting options

Very easy operation

Teach-in and threshold value adjustment using the • and • buttons
2 LEDs • Green: status and yellow: switching output

Qualitative diagnostics

binary using the red LED

Fast and precise

- Activation time of just 0.25 ms
- Up to a maximum of 250 m/min of label material (in operation and teach-in process)
- High reproducibility: only ±0.2 mm of deviation

High flexibility

thanks to ultrasound and a fork width of 6 mm and a fork depth of 70 mm for a wide variety of label material such as:

- Metalized foil labels
- Transparent labels
- Paper labels
- Booklets up to a thickness of 6 mm
- Ultra-short labels with only 2 mm of length

High process reliability

2 independent switching outputs and potential parallel operation: fast switching output during ongoing IO-Link communication

Operation with process reliability

Fast, efficient cleaning thanks to large blow-out hole



ONE LABEL SENSOR FOR A WIDE RANGE OF APPLICATIONS.

APPLICATION-SPECIFIC CONFIGURATION INSTEAD OF VARIOUS PIECES OF HARDWARE.

Instead of keeping various sensors on hand for different applications, you can save the application-specific configuration in the IO-Link master, load it to the sensor and get started right away. Device swapping and system duplication work just as easily.



Detection of transparent foil labels for application at a precise position **UGUTI 6/70**

The ultrasonic label sensor detects label gaps with precision and makes it possible to carry out accurate positioning of transparent labels

- High-performance labeler with ultrasonic label sensor for transparent labels
- Fork light barrier trigger sensor
- M12 ultrasonic sensor for determining the roller diameter

RELIABLE AND STABLE APPLICATIONS: UGUTI WITH IO-LINK



Multi-functional and standardized

Format change through threshold value adjustment and through job management with application-specific configurations in accordance with the Smart Sensor Profile



Parallel operation

Configuration/diagnostics using IO-Link and fast switching output simultaneously:



Qualitative and quantitative diagnostics:

Diagnostics

- Analysis of process stability and teach-in quality (qualitative)
- Current process values, min/max, teaching and threshold measured values (quantitative)

Easy maintenance

- Device swap without manual intervention or specialized knowledge thanks to IO-Link 1.1 with data storage in the master
- Smart Sensor Profile Fully compliant with standards



01010101000011101010101

IO-Link communication with pin 4


Fast switching output for switching bit with pin 2

Labeler

SMART THANKS TO IO-LINK. SAVE TIME AND MONEY.

GET STRAIGHT TO THE POINT.

IO-Link provides a point-to-point connection within any network, fieldbus or backplane bus. The IO-Link master can be installed either directly in the field or in the control cabinet. The international IO-Link standard (in accordance with IEC 61131-9) is now regarded as an **"enabler for Industry 4.0"**



5 REASONS FOR OUR UGUTI WITH IO-LINK.

 COST REDUCTION thanks to reduced stockkeeping One sensor can provide the solution for various applications by adjusting the configuration. Application-specific sensors are no longer necessary.
 IMPLEMENTATION OF INNOVATIVE MACHINE CONCEPTS thanks to consistent communication Recipe management in the IO-Link master, remote maintenance, diagnostics, sensor-configuration in accordance with the standardized Smart Sensor Profile
 REDUCTION OF COMMISSIONING TIMES through standard cabling and data storage in the master Standard plug connectors and push/pull outputs The sensor can be configured directly over the IO-Link master and is saved in the master with IO-Link 1.1
INCREASED MACHINE PRODUCTIVITY through configuration and identification

 Additional functionality integrated directly into the sensor: Sensor modes, teach-in, evaluation of signal values, pulse extension, operation lock

REVOLUTIONIZING MAINTENANCE through self-diagnostics and data storage

Process stability diagnostics (e.g. function reserve)

1

2

3

4

5

Easy device swapping without manual intervention or specialized knowledge thanks to data storage in IO-Link 1.1 master

TECHNICAL DATA UGUTI 6/70

	UGUTI 6/70 G6-B5	UGUTI 6/70 G6-RB5	IOL MASTER IO-LINK DEVICE TOOL
			CAN BE USED ANYWHERE
Housing dimensions H/W/D	45 / 90 / 18 mm	45 / 90 / 18 mm	for offline diagnostics and offline configuration
Fork/slot width	6 mm		
Slot depth	70 mm		
Indicators	Status Switching output Warning	LED: green LED: yellow LED: red	Version and the formation of the formati
Switching output	2 independent outputs, push-pull, 100 mA, NO/NC Additional warning output (for diagnostics) / output for parallel operation		
Interface	IO-Link		 Universal IO-Link 1-port master with USB 2.0
Internal power consumption	40 mA		(Mini USB B) interface and PC software
Activation time	0.25 ms		 For all devices with IODD Specification 1.0.1 and 1.1
Max. belt speed teach mode / operation	48000 labels/min ¹⁾		 Status LED for IO-Link and SIO mode
Reproducibility	± 0.2 mm ²⁾		 M12 connection for devices
Sensitivity adjustment using teach button	Yes		 Power supply for IO-Link Device:
Sensitivity adjustment using remote teaching	Yes		Up to 80 mA over USB connection, up to 1 A with AC adapter
Connector	M12 5-pin	M12 (radial) 5-pin	
Connection cable	V	5</td <td></td>	

¹⁾ 2 mm label and 2 mm gap ²⁾ Dependent on the label material and carrier material

SOLUTIONS. CLEVER. PRACTICAL.

di-soric Headquarters

Germany: di-soric GmbH & Co. KG | Steinbeisstrasse 6 | 73660 Urbach Phone +49 71 81 98 79-0 | Fax +49 71 81 98 79-179 | info@di-soric.com

di-soric Subsidiaries

Austria: di-soric Austria GmbH & Co. KG | Phone +43 7228 72 366 | info.at@di-soric.com France: di-soric SAS | Phone +33 476 61 65 90 | info@di-soric.fr Singapore: di-soric Pte. Ltd. | Phone +65 6634 38436 | info.sg@di-soric.com Switzerland: di-soric SNT AG | Phone +41 44 817 29 22 | info.ch@di-soric.com The Netherlands: di-soric B. V. | Phone +31 413 33 13 91 | info.nl@di-soric.com

For further information visit www.di-soric.com/international